



# DuraForm<sup>®</sup> Flex

Thermoplastic elastomer material with rubber-like flexibility and functionality.

## General Properties

MEASUREMENT	CONDITION	METRIC	U.S.
Density	ASTM 4164	0.44 g/cm <sup>3</sup>	0.44 g/cm <sup>3</sup>
Melting Point	DSC	192 °C	378 °C

## Mechanical Properties

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength, Ultimate	D638	1.8 MPa	262 psi
Elongation at Break	D638	110 %	110 %
Tensile Modulus	D638	7.4 MPa	1080 psi
Flexural Modulus (@ 23° C)	D790	4.9 MPa	
Hardness, Shore D	D2240	45 - 75	45 - 75
Initial Tear Resistance (Die C @ 23 °C)	D624	15.1 J/m	86 lb/in
Abrasion Resistance Taber, CS-17 Wheel, 1 Kg Load	D4060	83.5 J/m (per 1000 cycles)	83.5 J/m (per 1000 cycles)

\* All data generated using 3D Systems recommended recycle rates

## Features

- Durable with good tear resistance
- Vary Shore A hardness without changing material
- Easy-to-process
- Good powder recycle characteristics
- Good surface finish and feature detail



[www.3dsystems.com](http://www.3dsystems.com)

### UK

Tel: +44 1442 282 600  
[info@3dsystems-europe.com](mailto:info@3dsystems-europe.com)

### USA

Tel: +1 803.326.3900  
[moreinfo@3dsystems.com](mailto:moreinfo@3dsystems.com)

**Germany, Scandinavia,  
 Eastern Europe, Middle East**

Tel: +49 6151 357 0  
[info@3dsystems-europe.com](mailto:info@3dsystems-europe.com)

### Asia-Pacific

Melbourne Tel: +61 3 9819 4422  
 Sydney Tel: +61 2 9516 5571  
[3dprinters.asiapac@3dsystems.com](mailto:3dprinters.asiapac@3dsystems.com)

Warranty/Disclaimer: Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2017 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. The 3D logo and Accura are registered trademarks of 3D Systems, Inc.