



# Accura<sup>®</sup> CastPro<sup>™</sup>

## Casting Class

Highly accurate material for stable investment casting patterns using QuickCast<sup>™</sup> technology

### Post-Cured Material

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength (MPa/PSI)	ASTM D 638	52-53	7540-7690
Tensile Modulus (MPa/KSI)	ASTM D 638	2490-2620	361000-380000
Elongation at Break (%)	ASTM D 638	4.1-8.3	4.1-8.3
Flexural Strength (MPa/PSI)	ASTM D 790	82-84	11890-12180
Flexural Modulus (MPa/KSI)	ASTM D 790	2310-2340	335000-339000
Impact Strength (J/m /Ft-lbs/in)	ASTM D 256	43-49.5	0.80-0.92
Heat Deflection Temperature	ASTM D 648 @ 66 PSI @ 264 PSI	51 50	124 122
Coefficient of Thermal Expansion (CTE)	ASTM E 831-93 0-40 °C 50-140 °C	102.9 160.2	57.2 89
Water Absorption (%)	ASTM D 570-98	0.33	0.33
Glass Transition (Tg)	DMA, E''	60-62	140-144
Hardness, Shore D		85	85

### Features

- Produce accurate QuickCast<sup>™</sup> patterns
- Excellent humidity/moisture resistance
- High production speed

### Liquid Material

MEASUREMENT	CONDITION	VALUE
Viscosity	@ 30 °C (86 °F)	250 cps
Penetration Depth (Dp)		6.2 mils
Critical Exposure (Ec)		8.7 mJ/cm <sup>2</sup>
Color		Clear Amber
Solid Density	@ 25 °C (77 °F)	1.17 g/cm <sup>3</sup>
Liquid Density	@ 25 °C (77 °F)	1.08 g/cm <sup>3</sup>



[www.3dsystems.com](http://www.3dsystems.com)

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2020 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo, and Accura are registered trademarks and CastPro, QuickCast are trademarks of 3D Systems, Inc.